



PENA55GAL

by Burndy
Catalog ID: PENA55GAL

Sealing Compound, 600 V, Viscosity: 305 At 100 DEG F, Size: 55 GAL,
Container: Drum

Product Details

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Drum
Pour Point	-15 °F
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
UPC	781810023587
UPC 12 Digit	7818100235877
Viscosity at 100 Fahrenheit	305 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	55 Gallon
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)