



## PENE55GAL

by Burndy  
Catalog ID: PENE55GAL

Penetrox 55 Gallon Drum

### Product Details

---

#### General

Application - For Use On	Copper to Copper
Container Type	Drum
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810023594
UPC 12 Digit	7818100235944
Viscosity at 100 Fahrenheit	250 °F

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

#### Logistics

Container Size	55 Gallon
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)