



PENEGAL

by Burndy
Catalog ID: PENEGAL

Electrical sealing compound, For Use On-Application: Copper to Copper

Product Details

General

Application - For Use On	Copper to Copper
Container Type	Can
Pour Point	-40 °F
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
UPC	781810593509
UPC 12 Digit	7818105935099
Viscosity at 100 Fahrenheit	250 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	1 Gallon
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)