



PG1825X03D

by Burndy
Catalog ID: PG1825X03D

Uninsulated Quick Disconnect Piggyback Terminals, #18- #22 AWG, .79"
L, .25" W

Product Details

General

Connector Type	Quick Disconnect Piggyback
Material	Brass
Plated	Y
Plating Type	Tin
Type	Disconnect Connectors
UPC	781810530597
UPC 12 Digit	7818105305977

Dimensions

Dimension - B Length inch	0.17 in
Dimension - Length Overall inch	0.79 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor Range	#22 AWG to #18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)