

PGHS1825X03D

by Burndy
Catalog ID: PGHS1825X03D

Heat Shrink Insul PigTail Disconnects, 18-22 AWG, 0.91" L, 0.25" W, Blue(Insul Color), 0.157 Bullet Size.

Made from pure copper, annealed for maximum strength,Color-coded, imprinted with wire size



Product Details

General

Application	For Use on Copper Conductor
Sub Brand	HYDENT
Type	Electrical Terminal
UPC	781810524084
UPC 12 Digit	7818105240844

Dimensions

Dimension - B Length inch	0.17 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)