



PGN1025X03B

by Burndy
Catalog ID: PGN1025X03B

Piggy-Back Terminal, 10-12 AWG, Bulk packaging, Nylon Insulated, Tin plated Brass

Product Details

General

| | |
|-----------------|-----------------------|
| Connector Type | Piggy back Terminal |
| Insulation | Y |
| Insulation Type | Nylon |
| Material | Brass |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | FINGRIP™ |
| Type | Disconnect Connectors |
| UPC | 781810327265 |
| UPC 12 Digit | 7818103272655 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length fraction | 0.27 |
| Dimension - B Length inch | 0.27 in |
| Dimension - L Length Overall mm | 24 mm |
| Dimension - Length Overall inch | 0.95 in |
| Dimension - Strip Length inch | 3/8 in |
| Dimension - Width inch | 0.28 in |
| Dimension - Width mm | 7 mm |

Conductor Related

| | |
|-----------------|--|
| Conductor Range | #12 AWG to #10 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 500 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)