



PGN1425X03B

by Burndy
Catalog ID: PGN1425X03B

Piggy-Back Terminal, 14-16 AWG, Bulk packaging, Nylon Insulated, Tin plated Brass

Product Details

General

Color	Blue
Connector Type	Piggy back Terminal
Insulation	Y
Insulation Type	Nylon
Material	Brass
Physical Attribute - Tongue Type	Disconnect
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327258
UPC 12 Digit	7818103272588

Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - Inside Diameter inch	0.091 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)