



PGN1425X03D

by Burndy
Catalog ID: PGN1425X03D

Piggy-Back Terminal, 14-16 AWG, Nylon Insulated, Tin plated Brass

Product Details

General

| | |
|-----------------|-----------------------|
| Connector Type | Piggy back Terminal |
| Insulation | Y |
| Insulation Type | Nylon |
| Material | Brass |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | FINGRIP™ |
| Type | Disconnect Connectors |
| UPC | 781810293102 |
| UPC 12 Digit | 7818102931022 |

Dimensions

| | |
|---|---------|
| Dimension - B Length fraction | 0.17 |
| Dimension - B Length inch | 0.17 in |
| Dimension - F Width Center to Center inch | 0.09 in |
| Dimension - L Length Overall mm | 23 mm |
| Dimension - Length Overall inch | 0.87 in |
| Dimension - Strip Length inch | 3/8 in |
| Dimension - Width inch | 0.28 in |
| Dimension - Width mm | 7 mm |

Conductor Related

| | |
|-----------------|--|
| Conductor Range | #14 AWG to #16 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 600 EA |
| Minimum Pack Quantity | 50 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)