



## PGN1825X03D

by Burndy  
Catalog ID: PGN1825X03D

Prop 65 Notice

Piggy-Back Terminal, 18-22 AWG, Nylon Insulated, Tin plated Brass

## Product Details

### General

Connector Type	Piggy back Terminal
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293096
UPC 12 Digit	7818102930966

### Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - F Width Center to Center inch	0.07 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

### Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

**Logistics**

Carton Quantity	600 EA
Minimum Pack Quantity	50

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)