



## PGP1025X03B

by Burndy  
Catalog ID: PGP1025X03B

Prop 65 Notice

Male/Female Quick Disconnect, Piggyback terminals, Vinyl Insulated, 10-12 AWG, Bulk

## Product Details

### General

|                 |                       |
|-----------------|-----------------------|
| Connector Type  | Piggy back Terminal   |
| Insulation      | Y                     |
| Insulation Type | Vinyl                 |
| Material        | Brass                 |
| Plated          | Y                     |
| Plating Type    | Tin                   |
| Trade Name      | FINGRIP™              |
| Type            | Disconnect Connectors |
| UPC             | 781810327210          |
| UPC 12 Digit    | 7818103272100         |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length fraction   | 0.27    |
| Dimension - B Length inch       | 0.27 in |
| Dimension - L Length Overall mm | 24 mm   |
| Dimension - Length Overall inch | 0.95 in |
| Dimension - Strip Length inch   | 3/8 in  |
| Dimension - Width inch          | 0.28 in |
| Dimension - Width mm            | 7 mm    |

### Conductor Related

|                 |                                                                                              |
|-----------------|----------------------------------------------------------------------------------------------|
| Conductor Range | #12 AWG to #10 AWG                                                                           |
| Conductor Type  | <ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul> |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 500 |
|-----------------------|-----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)