



## PGP1025X03D

by Burndy  
Catalog ID: PGP1025X03D

Prop 65 Notice

Male/Female Quick Disconnect, Piggyback terminals, Vinyl Insulated, 10-12 AWG

## Product Details

### General

Connector Type	Piggy back Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293089
UPC 12 Digit	7818102930899

### Dimensions

Dimension - B Length fraction	0.27
Dimension - B Length inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

**Logistics**

Carton Quantity	600 EA
Minimum Pack Quantity	50

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)