



## PGP1425X03B

by Burndy  
Catalog ID: PGP1425X03B

Prop 65 Notice

Male/Female Quick Disconnect, Piggyback terminals, Vinyl Insulated, 14-16 AWG, Bulk

### Product Details

#### General

Color	Blue
Connector Type	Piggy back Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Physical Attribute - Tongue Type	Disconnect
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327203
UPC 12 Digit	7818103272033

#### Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - Inside Diameter inch	0.091 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.91 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

#### Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Type	CU C Str-Size

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1000
-----------------------	------

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)