



## PGP1425X03D

by Burndy  
Catalog ID: PGP1425X03D

Prop 65 Notice

Male/Female Quick Disconnect, Piggyback terminals, Vinyl Insulated, 14-16 AWG

## Product Details

### General

|                 |                       |
|-----------------|-----------------------|
| Connector Type  | Piggy back Terminal   |
| Insulation      | Y                     |
| Insulation Type | Vinyl                 |
| Material        | Brass                 |
| Plated          | Y                     |
| Plating Type    | Tin                   |
| Trade Name      | FINGRIP™              |
| Type            | Disconnect Connectors |
| UPC             | 781810293072          |
| UPC 12 Digit    | 7818102930722         |

### Dimensions

|   |         |
|---|---------|
| Dimension - B Length fraction             | 0.17    |
| Dimension - B Length inch                 | 0.17 in |
| Dimension - F Width Center to Center inch | 0.09 in |
| Dimension - L Length Overall mm           | 23 mm   |
| Dimension - Length Overall inch           | 0.91 in |
| Dimension - Strip Length inch             | 3/8 in  |
| Dimension - Width inch                    | 0.28 in |
| Dimension - Width mm                      | 7 mm    |

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #14 AWG to #16 AWG |
| Conductor Type  | CU C Str-Size      |

### Certifications and Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | No    |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 600 EA |
| Minimum Pack Quantity | 50     |

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)