



PGP1825X03D

by Burndy
Catalog ID: PGP1825X03D

Prop 65 Notice

Male/Female Quick Disconnect, Piggyback terminals, Vinyl Insulated, 18-22 AWG

Product Details

General

Connector Type	Piggy back Terminal
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293065
UPC 12 Digit	7818102930655

Dimensions

Dimension - B Length fraction	0.17
Dimension - B Length inch	0.17 in
Dimension - F Width Center to Center inch	0.07 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.91 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)