

PT2990010

by Burndy
Catalog ID: PT2990010

Prop 65 Notice

Hydraulic hose, 10 ft, non-conductive hose. minimum burst pressure is 40,000 psi nominal working pressure is 10,000 psi.

10 FT - 3/16 IN diameter - non conductive hose with stack-able couplers (male/female) - orange, 10000PSI



Product Details

General

Application	High pressure hose assembly
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810625668

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)