



PT2990025

by Burndy
Catalog ID: PT2990025

Prop 65 Notice

Insulated Hydraulic Hose, 25 ft x 3/16" Dia, Male/Female Couplers, use with 10,000 PSI only

- 10,000 PSI
- Orange
- Non-Conductive
- Stackable couplers (male/female)

Features: 25 FT-3/16 IN diameter-Non Conductive hose with stackable couplers(male/female), 10000 PSI

Product Details

General

Application	High pressure Hose Assembly
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810008478

Dimensions

Length	25 ft
Weight	5.64 lb
Width	0.187 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)