

PT2990110

by Burndy
Catalog ID: PT2990110

Prop 65 Notice

Hydraulic hose, non-conductive hose. Minimum burst pressure is 40,000 psi nominal working pressure is 10,000 psi.

10 FT - 1/4 IN diameter - non conductive hose with stack-able couplers (male/female) - orange, 10000PSI



Product Details

General

Application	High pressure hose assembly
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810008485

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)