



## PT2990115

by Burndy  
Catalog ID: PT2990115

Prop 65 Notice

Hydraulic hose, 15 ft, non-conductive hose. minimum burst pressure is 40,000 psi nominal working pressure is 10,000 psi.

15 FT- 1/4 IN diameter - non conductive hose with stack-able couplers (male/female) - orange, 10000PSI

## Product Details

### General

Application	High pressure hose assembly
Sub Brand	TOOLING ACCESSORY
Type	Hydraulic Accessories
UPC	781810008492

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)