



PT2990125

by Burndy
Catalog ID: PT2990125

Prop 65 Notice

Hydraulic hose, 25 ft, non-conductive hose. minimum burst pressure is 40,000 psi nominal working pressure is 10,000 psi.

1/4 dia hose provides higher flow rate for faster ram movement

Product Details

General

Application	Leather Holster for Mechanical Full Cycle Ratchet Crimping Tool
Sub Brand	HYDRAULIC HOSE
Type	Hydraulic Accessories
UPC	781810008508

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)