



PTV14

by Burndy
Catalog ID: PTV14

Cu Pin Terminal, 14-16 AWG, 0.80" L, 0.07" W, Molded Vinyl Insul, Tin Plated, Blue(Insul Color)

Product Details

General

UPC	781810530610
UPC 12 Digit	7818105306100

Dimensions

Dimension - B Length inch	0.19 in
Dimension - Length Overall inch	0.8 in
Dimension - Pad Size inch	0.41 in
Dimension - Pad Width inch	0.07 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)