



## Q10F25X03D

by Burndy  
Catalog ID: Q10F25X03D

Prop 65 Notice

Brass Female Quick Disconnect, 12-10 AWG, Chamfered Barrel Opening, Tin Plated.

Butted seam, Insulated connectors

## Product Details

### General

Application	Female Disconnect
Connector Type	Female Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293546
UPC 12 Digit	7818102935466

### Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.250 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	600 EA
-----------------	--------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)