



## Q10M25X03D

by Burndy  
Catalog ID: Q10M25X03D

Prop 65 Notice

Tin-Plated Brass Non-Insulated Male Quick Disconnects, 10 - 12 AWG, Butted seam, Chamfered barrel opening, Mates with dimpled female socket detent.

Features: Butted Seam, Chamfered Barrel Opening: Assures Quick And Easy Wire Insertion, Dimpled Female Socket Detent

## Product Details

### General

Application	Male Disconnect
Connector Type	Male Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525036
UPC 12 Digit	7818105250366

### Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.250 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)