



Q14M18X02B

by Burndy
Catalog ID: Q14M18X02B

Tin-Plated Brass Non Insulated Female Quick Disconnects, #14 - #16
AWG, .66" L, .187" W, Wire Strip Length- 3/8"

Product Details

General

| | |
|------------------------|-----------------------|
| Connector Type | Male Disconnect |
| Feature - Barrel Style | Chamfered |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | FINGRIP™ |
| Type | Disconnect Connectors |
| UPC | 781810327821 |
| UPC 12 Digit | 7818103278211 |

Dimensions

| | |
|---|---------|
| Dimension - B Length fraction | 6/25 in |
| Dimension - B Length inch | 0.24 in |
| Dimension - F Width Center to Center inch | 0.08 in |
| Dimension - Length Overall inch | 0.64 in |
| Dimension - Width inch | 0.19 in |
| Dimension - Width mm | 5 mm |

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - Copper Str Size | 16 AWG;14 AWG |
| Conductor - Copper Str Size Range | 16 AWG-14 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |

| |
|-----------|
| UL Listed |
|-----------|

| |
|----|
| No |
|----|

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|------|
| 1000 |
|------|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)