



## Q18M18X02D

by Burndy  
Catalog ID: Q18M18X02D

Prop 65 Notice

Tin-Plated Brass Non-Insulated Male Quick Disconnects, 18-22 AWG, Butted seam, Chamfered barrel opening.

Features: Butted Seam, Chamfered Barrel Opening: Assures Quick And Easy Wire Insertion, Dimpled Female Socket Detent: Ensures Firm Grip, Mates with Type Q-F Female disconnects, Size: 0.55 IN Overall Length X 0.17 IN Barrel Length X 0.19 IN Width, Installation Tool: MR20, Y10D Tool, Nema Tab Size: 0.187 X 0.2 IN

## Product Details

### General

Application	For quickly connecting or disconnecting a terminal
Connector Type	Male Disconnect
Feature - Barrel Style	Chamfered
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293249
UPC 12 Digit	7818102932499

### Dimensions

Dimension - Length Overall inch	0.66 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.187 in
Dimension - Width mm	5 mm

### Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG-18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

## Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)