



## Q18M25X03D

by Burndy  
Catalog ID: Q18M25X03D

Prop 65 Notice

Tin-Plated Brass Non-Insulated Male Quick Disconnects, 18-22 AWG, Butted seam, Chamfered barrel opening, Mates with dimpled female socket detent.

Features: Butted Seam, Chamfered Barrel Opening: Assures Quick And Easy Wire Insertion, Dimpled Female Socket Detent: Ensures Firm Grip, Mates with Type Q-F Female disconnects, Installation Tool: MR20, Y10D Tool, Size: 0.67 IN Overall Length X 0.17 IN Barrel Length X 0.25 IN Width, Nema Tab Size: 0.25 X 0.32 IN

## Product Details

### General

|                        |  |
|------------------------|--|
| Application            | For quickly connecting or disconnecting a terminal |
| Connector Type         | Male Disconnect                                    |
| Feature - Barrel Style | Chamfered  |
| Material               | Brass  |
| Plated                 | Y  |
| Plating Type           | Tin  |
| Sub Brand              | FINGRIP  |
| Trade Name             | FINGRIP™   |
| Type                   | Disconnect Connectors                              |
| UPC                    | 781810293263                                       |
| UPC 12 Digit           | 7818102932633                                      |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - Length Overall inch | 0.66 in  |
| Dimension - Strip Length inch   | 3/8 in   |
| Dimension - Width inch          | 0.250 in |
| Dimension - Width mm            | 6 mm     |

### Conductor Related

|                                   |  |
|-----------------------------------|--|
| Conductor - Copper Str Size       | 20 AWG;18 AWG  |
| Conductor - Copper Str Size Range | 20 AWG-18 AWG  |
| Conductor Type                    | <ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |

|           |    |
|-----------|----|
| UL Listed | No |
|-----------|----|

## Logistics

|                       |         |
|-----------------------|---------|
| Carton Quantity       | 1200 EA |
| Minimum Pack Quantity | 100     |

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)