

Q2A344N

by Burndy
Catalog ID: Q2A344N

Prop 65 Notice

Copper Terminal, 4 Hole, 400-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 2 Screws.

Features: Compact, high copper alloy terminal for joining two cables to equipment pads or bars, Each element accommodates a wide range of cable



Product Details

General

Application	For Copper Cable
Connector Type	Terminal
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810322208
UPC 12 Digit	7818103222088

Dimensions

Dimension - B Length inch	1.62 in
Dimension - D inch	3.09 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.69 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Stud Size inch	1/2

Dimension - Width fraction	3-3/4 in
Dimension - Width inch	3.75 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)