



Q3A344N

by Burndy
Catalog ID: Q3A344N

Prop 65 Notice

Copper Terminal, 4 Hole, 400-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 3 Screws.

Features: Compact, high copper alloy terminal for joining three cables to equipment pads or bar, Each element accommodates a wide range of cable

Product Details

General

Application	For Copper Cable
Connector Type	Terminal
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810323649
UPC 12 Digit	7818103236499

Dimensions

Dimension - D inch	3.13 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	1-15/16
Dimension - Height inch	2.00 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.69 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.00 in
Dimension - Stud Size inch	1/2
Dimension - Width fraction	4-9/16 in

Dimension - Width inch	4.56 in
Dimension - Width mm	116 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Size	400 Kcmil;500 Kcmil
Conductor - Copper Str Size Range	400 Kcmil-500 Kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)