



QA1CBNK

by Burndy
Catalog ID: QA1CBNK

Prop 65 Notice

High Cu Alloy Terminal, Heavy Duty, 1 Hole, #4 - #1 Str Commercial, 30 - 75 Navy, 1 Screw, Nickel Plated, 0.28" Hole Dia

Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Nickel Plated
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810500132
UPC 12 Digit	7818105001322

Dimensions

Dimension - D inch	0.75 in
Dimension - Height inch	1.00 in
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	1.75 in
Dimension - N inch	0.34 in
Dimension - Pad Width inch	0.62 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Navy Size	30 (19) Navy;40 (19) Navy;50 (19) Navy;60 (37) Navy;75 (37) Navy
Conductor - Copper Str Navy Size Range	30 (19) Navy-75 (37) Navy
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size Range	4 AWG-1 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	24
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)