



QA26B

by Burndy
Catalog ID: QA26B

Prop 65 Notice

Copper Terminal, Heavy Duty, 1 Hole, 1/0-2/0 AWG (Str), 3/8" Stud, 1 Screw.

Features: Heavy Duty, Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Fast Onwrench Installation, Conductor Type: Run: Commercial Stranded Copper, Navy Copper, Stud/bolt Hole Size: 3/8 IN, Length: 2 IN, Installation Torque: 180 IN-LB, Dimension T: 7/32 IN, Width: 13/16 IN, Height: 1-3/16 IN, Tongue Width : 13/16 IN, Dimension D: 1 IN, Dimension K: 13/32 IN, Dimension N: 7/16 IN, Number Of Clamping Elements: 1

Product Details

General

Application	For Joining A Wide Range Of Cable To Equipment Pads Or Bar
Connector Type	Terminal
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810314128
UPC 12 Digit	7818103141288

Dimensions

Dimension - D inch	0.94 in
Dimension - Height fraction	1-3/16
Dimension - Height inch	1.12 in
Dimension - Hole Size fraction	13/32
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	0.81 in

Dimension - Stud Size inch	3/8
----------------------------	-----

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy;125 (61) Navy
Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy
Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)