

QA282B

by Burndy
Catalog ID: QA282B

Prop 65 Notice

Copper Terminal, Heavy Duty, 2 Hole, 3/0-4/0 AWG (Str), 3/8" Stud, 1" Stud Hole Spacing, 1 Screw.

Features: Type QA Heavy Duty, Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Bar



Product Details

General

| | |
|---------------------------------------|-------------------------|
| Application | For Copper Cable |
| Connector Type | Terminal |
| Installation Torque Recommended in-lb | 250 LBS/in |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Number of Screws | 1 |
| Physical Attribute - Screw Type | Hexagonal Bolt |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | QIKLUG |
| Temperature Rating | 194 |
| Trade Name | QIKLUG™ |
| Type | Bolted Lugs & Terminals |
| UPC | 781810314920 |
| UPC 12 Digit | 7818103149200 |

Dimensions

| | |
|---|-----------|
| Dimension - B Length fraction | 1-1/33 in |
| Dimension - B Length inch | 1.03 in |
| Dimension - D inch | 2.00 in |
| Dimension - F Width Center to Center inch | 1.00 in |
| Dimension - Height fraction | 1-9/29 in |
| Dimension - Height inch | 1.31 in |
| Dimension - Hole Size fraction | 13/32 |
| Dimension - Hole Size inch | 0.41 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 81 mm |
| Dimension - Length Overall inch | 3.19 in |
| Dimension - N inch | 0.44 in |
| Dimension - Pad Width inch | 1.00 in |

| | |
|----------------------------|-----|
| Dimension - Stud Size inch | 3/8 |
|----------------------------|-----|

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Conductor Related

| | |
|--|--|
| Conductor - Copper Str Navy Size | 150 (61) Navy;200 (61) Navy |
| Conductor - Copper Str Navy Size Range | 150 (61) Navy-200 (61) Navy |
| Conductor - Copper Str Size | 3/0 AWG;4/0 AWG |
| Conductor - Copper Str Size Range | 3/0 AWG-4/0 AWG |
| Conductor Type | <ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)