



QA44B

by Burndy
Catalog ID: QA44B

Prop 65 Notice

Copper Terminal, Heavy Duty, 1 Hole, 850-1000 kcmil, 5/8" Stud, 1 Screw.

Features: Type QA Heavy Duty, Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Fast One Wrench Installation, Number Of Clamping Elements: 1, Dimension N: 1 IN, Dimension K: 11/16 IN, Stud/bolt Hole Size: 5/8 IN, Dimension D: 2 IN, Dimension T: 1/2 IN, Conductor Type: Run: Commercial Stranded Copper, Navy Copper, Tongue Width: 1-7/8 IN, Height: 2-3/4 IN, Installation Torque: 500 IN-LB, Length: 3-15/16 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bars
Connector Type	Terminal
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810317563

Dimensions

Dimension - D inch	2.00 in
Dimension - Height fraction	2-1/2
Dimension - Height inch	2.50 in
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	100 mm
Dimension - Length Overall inch	3.94 in
Dimension - N inch	1 in
Dimension - Pad Width inch	1.88 in
Dimension - Stud Size inch	5/8
Dimension - Width mm	48 mm
Weight	1.7 lb

Conductor Related

Conductor - Copper Str Navy Size	1000 (127) Navy
Conductor - Copper Str Navy Size Range	1000 (127) Navy
Conductor - Copper Str Size	900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	850 kcmil-1000 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)