

## QA462B

by Burndy  
Catalog ID: QA462B

High Cu Alloy Terminal, Heavy Duty, 2 Holes, 1100 - 1500 kcmil  
Commercial, 1300 Navy, 1 Screw, 1/2" Stud



## Product Details

### General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810318003

### Dimensions

Dimension - D inch	2.62 in
Dimension - Height inch	2.88 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	124 mm
Dimension - Length Overall inch	4.88 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	2.12 in
Dimension - Width mm	54 mm
Weight	2.9 lb

### Conductor Related

Conductor - Copper Str Navy Size	1300 (127) Navy
Conductor - Copper Str Navy Size Range	1300 (127) Navy
Conductor - Copper Str Size	1250 kcmil;1300 kcmil;1500 kcmil
Conductor - Copper Str Size Range	1100 kcmil-1500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Str Navy-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)