

# QA46B

by Burndy  
Catalog ID: QA46B

Prop 65 Notice

Copper Terminal, Heavy Duty, 1 Hole, 1100-1500 kcmil, 3/4" Stud, 1 Screw



## Product Details

### General

Connector Type	Terminal
Installation Torque Recommended in-lb	600 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810317969

### Dimensions

Dimension - D inch	2.12 in
Dimension - Height fraction	3-1/8
Dimension - Height inch	2.88 in
Dimension - Hole Size fraction	13/16
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.38 in
Dimension - N inch	1.06 in
Dimension - Pad Width inch	2.12 in
Dimension - Stud Size inch	3/4
Dimension - Width mm	54 mm
Weight	2.7 lb

### Conductor Related

Conductor - Copper Str Navy Size	1300 (127) Navy
Conductor - Copper Str Navy Size Range	1300 (127) Navy
Conductor - Copper Str Size	1100kcmil;1300 kcmil;1500 kcmil

Conductor - Copper Str Size Range	1100 kcmil-1500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Str Navy-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	3
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)