



QB1C

by Burndy
Catalog ID: QB1C

Prop 65 Notice

Copper Terminal, Side Entrance, 1 Hole, 4-1 AWG (Str), 1/4" Stud, 1 Screw.

Features: Compact, High Copper Alloy Side Entrance Terminal For Joining A Range Of Cable At Right Angles To Terminal Blocks, One-Wrench Installation, Dimension N: 11/32 IN, Dimension D: 13/16 IN, Number Of Clamping Elements: 1, Dimension T: 7/32 IN, Dimension K: 9/32 IN, Installation Torque: 150 IN-LB, Tongue Width: 11/16 IN, Height: 1 IN, Length: 1-1/2 IN, Stud/bolt Hole Size: 1/4 IN

Product Details

General

Application	For Joining A Range Of Copper Cable At Right Angles To Terminal Blocks
Connector Type	Terminal
Installation Torque Recommended in-lb	150 LBS/in
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324042

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - D inch	0.81 in
Dimension - Height inch	1.00 in
Dimension - Hole Size fraction	9/32
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - N inch	0.34 in
Dimension - Pad Width fraction	11/16 in
Dimension - Pad Width inch	0.63 in

Dimension - Stud Size fraction	1/4
Dimension - Width inch	0.625 in
Dimension - Width mm	16 mm
Weight	0.13 lb

Conductor Related

Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size Range	4 AWG-1 AWG
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)