



QB26

by Burndy
Catalog ID: QB26

Prop 65 Notice

Copper Terminal, Side Entrance, 1 Hole, 1/0-2/0 AWG (Str), 3/8" Stud, 1 Screw.

Features: Compact, High Copper Alloy Side Entrance Terminal For Joining A Range Of Cable At Right Angles To Terminal Blocks, One-Wrench Installation, Number Of Clamping Elements: 1, Dimension D: 1 IN, Dimension N: 7/16 IN, Dimension T: 7/32 IN, Dimension K: 13/32 IN, Tongue Width: 13/16 IN, Installation Torque: 180 IN-LB, Stud/bolt Hole Size: 3/8 IN, Height: 1-1/32 IN, Length: 1-13/16 IN

Product Details

General

Application	For Joining A Range Of Copper Cable At Right Angles To Terminal Blocks
Connector Type	Terminal
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324288

Dimensions

Dimension - B Length fraction	47/50 in
Dimension - B Length inch	0.94 in
Dimension - D inch	1.00 in
Dimension - Height fraction	1-1/8
Dimension - Height inch	1.13 in
Dimension - Hole Size fraction	13/32
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - N inch	0.44 in
Dimension - Pad Width fraction	13/16 in
Dimension - Pad Width inch	0.81 in

Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Width inch	0.81 in
Dimension - Width mm	21 mm
Weight	0.23 lb

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)