



QB34

by Burndy
Catalog ID: QB34

Prop 65 Notice

Cu Alloy Side Entrance Terminal, 400 - 500 kcmil, 1 Pad Hole

Product Details

General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	621945037441

Dimensions

Dimension - B Length fraction	1-19/50 in
Dimension - B Length inch	1.38 in
Dimension - D inch	1.75 in
Dimension - Height fraction	1-15/16 in
Dimension - Height inch	1-15/16
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19
Dimension - N inch	0.81 in
Dimension - Pad Width inch	1.38 in
Weight	0.82 lb

Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)