



QB4C

by Burndy
Catalog ID: QB4C

Prop 65 Notice

Copper Terminal, Side Entrance, 1 Hole, 8-4 AWG (Str), 1/4" Stud, 1 Screw

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	110 LBS/in
Material	Copper
Physical Attribute - Number of Clamping Elements	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810324202

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.84 in
Dimension - Height fraction	1-1/32
Dimension - Height inch	1.03 in
Dimension - Hole Size fraction	9/32
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - N inch	0.38 in
Dimension - Pad Width fraction	11/16 in
Dimension - Pad Width inch	0.63 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Width inch	0.70 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	8 AWG-4 AWG
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	33
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)