



QDA26

by Burndy
Catalog ID: QDA26

Prop 65 Notice

Copper Terminal, 1 Hole, 1/0-2/0 AWG (Str), 1/2" Stud, 1 Screw.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Dimension T: 5/16 IN, Stud/bolt Hole Size: 1/2 IN, Dimension K: 9/16 IN, Tongue Width: 1-1/4 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Length: 2-1/2 IN, Installation Torque: 180 IN-LB, Height: 1-3/16 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325162

Dimensions

Dimension - Cross Flats inch	0.69 in
Dimension - Height fraction	1-3/16
Dimension - Height inch	1.19 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Pad Width inch	1.25 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Conductor Related

Conductor - Copper Str Navy Size	100 (61) Navy;125 (61) Navy
----------------------------------	-----------------------------

Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy
Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)