



QDA28

by Burndy
Catalog ID: QDA28

Prop 65 Notice

Copper Terminal, 1 Hole, 3/0-4/0 AWG (Str), 1/2" Stud, 1 Screw.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Dimension K: 9/16 IN, Dimension T: 5/16 IN, Stud/bolt Hole Size: 1/2 IN, Tongue Width: 1-1/4 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Installation Torque: 250 IN-LB, Length: 2-5/8 IN, Height: 1-5/16 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	250 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325322

Dimensions

Dimension - Height fraction	1-5/16
Dimension - Height inch	1.31 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.63 in
Dimension - Pad Width inch	1.25 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Conductor Related

Conductor - Copper Str Navy Size	150 (61) Navy;200 (61) Navy
Conductor - Copper Str Navy Size Range	150 (61) Navy-200 (61) Navy

Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)