



QDA31

by Burndy
Catalog ID: QDA31

Prop 65 Notice

Copper Terminal, 1 Hole, 250-350 kcmil, 5/8" Stud, 1 Screw.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Stud/bolt Hole Size: 5/8 IN, Dimension K: 11/16 IN, Dimension T: 5/16 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Tongue Width: 1-1/2 IN, Height: 1-11/16 IN, Length: 3 IN, Installation Torque: 325 IN-LB

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	325 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325407

Dimensions

Dimension - Height fraction	1-11/16 in
Dimension - Height inch	1.69 in
Dimension - Hole Size fraction	11/16
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.00 in
Dimension - Pad Width inch	1.50 in
Dimension - Stud Size inch	5/8
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy;300 (91) Navy;350 (91) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy-350 (91) Navy

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	250 kcmil-350 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)