



QDA34

by Burndy
Catalog ID: QDA34

Prop 65 Notice

Copper Terminal, 1 Hole, 400-500 kcmil, 3/4" Stud, 1 Screw.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Dimension T: 5/16 IN, Stud/bolt Hole Size: 3/4 IN, Dimension K: 13/16 IN, Tongue Width: 1-7/8 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Height: 2 IN, Length: 3-5/8 IN, Installation Torque: 375 IN-LB

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	375 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325568

Dimensions

Dimension - Height inch	2.00 in
Dimension - Hole Size fraction	13/16
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	97 mm
Dimension - Length Overall inch	3.63 in
Dimension - Pad Width inch	1.88 in
Dimension - Stud Size inch	3/4
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy;500 (127) Navy
----------------------------------	-------------------------------

Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Size	400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)