



QDA4C

by Burndy
Catalog ID: QDA4C

Prop 65 Notice

Copper Terminal, 1 Hole, 8-4 AWG (Str), 3/8" Stud, 1 Screw.

Features: Compact, High Copper Alloy Terminal For Joining A Wide Range Of Cable To Equipment Studs, Provides Low Contact Resistance When Gripped Between Two Contact Nuts, One Wrench Installation, Stud/bolt Hole Size: 3/8 IN, Dimension K: 7/16 IN, Dimension T: 7/32 IN, Tongue Width: 1 IN, Conductor Type: Run: Navy, Commercial Stranded Copper, Length: 1-7/8 IN, Installation Torque: 110 IN-LB, Height: 3/4 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Studs
Connector Type	Terminal
Installation Torque Recommended in-lb	110 LBS/in
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Bolted Lugs & Terminals
UPC	781810325001

Dimensions

Dimension - Cross Flats inch	0.56 in
Dimension - Height fraction	3/4
Dimension - Height inch	0.72 in
Dimension - Hole Size fraction	7/16
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Pad Width inch	1.00 in
Dimension - Stud Size inch	3/8
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - Copper Str Navy Size	23 (7) Navy;30 (19) Navy;40 (19) Navy
----------------------------------	---------------------------------------

Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	8 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)