



QGFL29B1

by Burndy
Catalog ID: QGFL29B1

Prop 65 Notice

Bartap, 6 Str. - 250 kcmil, Cable To Flat, 1/4 IN Thickness.

Features: High Copper Alloy BARTAP For Joining A Range Of Cable To Bar Or Pad, One-Wrench Installation, Can Be Installed Side By Side Or In Line On NEMA Drilled Bar, Wire Type: Copper, Conductor Clamping Hardware: 1/2 IN, Installation Torque: 480 IN-LB

Product Details

General

Application	Substation
Connector Type	Bus Bar Clamp and Accessories
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	BARTAP
Trade Name	BARTAP™
Type	QGFL
UPC	781810325124
UPC 12 Digit	7818103251244

Dimensions

Dimension - B Length fraction	1-2/5 in
Dimension - B Length inch	1.40 in
Dimension - Height fraction	2-5/8 in
Dimension - Height inch	2.63 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Copper Str Size	#6 Str;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	#6 Str-250 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)