



QGFL31B1

by Burndy
Catalog ID: QGFL31B1

Prop 65 Notice

Bartap, 2 Sol. - 350 kcmil, Cable To Flat.

Features: High Copper Alloy BARTAP For Joining A Range Of Cable To Bar Or Pad, One-Wrench Installation, Can Be Installed Side By Side Or In Line On NEMA Drilled Bar, Conductor Clamping Hardware: 1/2 IN, Wire Type: Copper, Installation Torque: 480 IN-LB

Product Details

General

| | |
|---------------------|-------------------------------|
| Application | Substation |
| Connector Type | Bus Bar Clamp and Accessories |
| Material | Copper Alloy |
| Material - Hardware | DURIUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | BARTAP |
| Trade Name | BARTAP™ |
| Type | QGFL |
| UPC | 781810005927 |
| UPC 12 Digit | 7818100059277 |

Dimensions

| | |
|-------------------------------|----------|
| Dimension - B Length fraction | 1-3/4 in |
| Dimension - B Length inch | 1.75 in |
| Dimension - Height fraction | 2-7/8 in |
| Dimension - Height inch | 2.88 in |
| Dimension - Width fraction | 1-5/8 in |
| Dimension - Width inch | 1.63 in |
| Dimension - Width mm | 41 mm |

Electrical Ratings

| | |
|--------------|--------|
| Rating - KVA | 230 kV |
|--------------|--------|

Conductor Related

| | |
|-------------------------------------|--|
| Conductor - Copper Solid Size | 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | 2 AWG-4/0 AWG |
| Conductor - Copper Str Size | 2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil |
| Conductor - Copper Str Size Range | 2 AWG-350 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size |

Certifications and Compliance

| | |
|---|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)