



## QN10F25X03D

by Burndy  
Catalog ID: QN10F25X03D

Prop 65 Notice

Brass Female Quick Disconnect, 12-10 AWG, Nylon Insulated, Funnel Entry, Tin Plated.

Features: Sleeved Barrel, Insulated Connectors: Eliminate The Need For Post Installation Insulation, Funnel Entry Barrel Opening: Assures Quick And Easy Wire Insertion, Dimpled Female Socket Detent: Ensures Firm Grip, Mates With Type QN-M Male Disconnects, 300 V Maximum, 105 DEG C Maximum, Installation Tool: Y10D Tool, Size: 0.97 IN Overall Length X 0.23 IN Barrel Length X 0.25 IN Width, Nema Tab Size: 0.25 X 0.32 IN, Temperature: 105 DEG C Maximum

## Product Details

### General

Application	For quickly connecting or disconnecting a terminal
Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293607
UPC 12 Digit	7818102936077

### Dimensions

Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)