



QN10M25X03D

by Burndy
Catalog ID: QN10M25X03D

Prop 65 Notice

Brass Male Quick Disconnects, Funnel Entry, 10-12 AWG, 300 V, 0.95" L, 0.25" W, Nylon Insul, Sleeved bbl, Tin Plated, Yellow(Insul Color).

Butted seam, Funnel entry barrel opening

Product Details

General

Application	Male Disconnect
Connector Type	Male Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525043
UPC 12 Digit	7818105250433

Dimensions

Dimension - Length Overall inch	0.95 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)