



QN14F11X02D

by Burndy
Catalog ID: QN14F11X02D

Prop 65 Notice

Brass Female Quick Disconnects, Funnel Entry, 14-16 AWG, 300 V, 0.77" L, 0.11" W, Nylon Insul, Sleeved bbl, Tin Plated, Blue(Insul Color).

Butted seam, Insulated connectors

Product Details

General

Application	Female Disconnect
Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810525616
UPC 12 Digit	7818105256166

Dimensions

Dimension - Length Overall inch	0.77 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.11 in
Dimension - Width mm	3 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI

UL Listed	No
-----------	----

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)