

## QN14F18X02B

by Burndy  
Catalog ID: QN14F18X02B

MATERIAL: TIN-PLATED BRASS. 300 VOLTS MAX. 105 C MAX.



## Product Details

### General

Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292761
UPC 12 Digit	7818102927611

### Dimensions

Dimension - Length Overall inch	0.79 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed
-----------

No
----

## Logistics

Minimum Pack Quantity
-----------------------

1000
------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)