



## QN14FF250D

by Burndy  
Catalog ID: QN14FF250D

Prop 65 Notice

Female Quick Brass Disconnect, 16-14 AWG, 600 V, Nylon Insulated, Tin Plated

## Product Details

### General

Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810038345

### Dimensions

Dimension - B Length fraction	19/50 in
Dimension - B Length inch	0.38 in
Dimension - D inch	0.16 in
Dimension - Length Overall inch	0.89 in
Dimension - Pad Width inch	0.23 in

### Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	600 EA
-----------------	--------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)