



## QN18F18X02B

by Burndy  
Catalog ID: QN18F18X02B

Female Brass Disconnect Terminal, 22-16 AWG, 0.79 in L, 0.19 in W, Nylon Insulated, Tin Plated, Bulk Packaging

## Product Details

### General

Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292679
UPC 12 Digit	7818102926799

### Dimensions

Dimension - Length Overall inch	0.79 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor Range	#22 AWG to #16 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Minimum Pack Quantity

1000

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)